


Center Tilt adjust ring

Tilt spacer (Copper Tape) Installed on QHY128C and QHY247C





Typically the Copper tape is 65um an 100um. One piece of the copper type can generate about 20-30um adjust results.

Use the focal plane analyze software to determind the direction that where you put this tape.

The advantage of this method to compare with the three screw focal adjust method

1. More stable. The copper film is more stable than the screws. On the three screw focal adjust method the force is focusing into the contact point of the screw. It may have issue in long term stablility
2. More easy to adjust. The distance and the direction of the position is easy to be get from the focal plane analyze software. No need to adjust for many times for the three screw adjustment method.